

Product data sheet

Characteristics

CLITPDL1C2B10

Clipsal - Lighting, Downlight LED, 750lm, 3K/4K/6K Trim, 10 Pack



Main

Range	Clipsal
Product or component type	Downlight
Device application	Lighting
Market segment	Residential Small commercial

Complementary

Device mounting	Recessed ceiling
Shape	Round
Type of installation	Indoor
Rated power in W	9 W
Light source	LED
Total system power	240 V AC 50 Hz
Luminous flux	700 Lm 3000 K 4000 K 6000 K
Colour rendering index	R _a =80
Bulb lifespan	50000 h
Beam angle	90 °
Load type	Dimmable LED
Device composition	Round white plastic fixed integral dimming driver soft glow Flex plug
Quantity per set	10
Trim width	110 mm
Trim height	65.5 mm
Cut-out dimensions	90 mm
Mounting depth	62.5 mm
Net weight	0.25 kg

Environment

IP degree of protection	IP44
Insulation contact rating	IC-4
Unified glare rating	< 22
Ambient air temperature for operation	-10...25 °C
Relative humidity	non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.5 cm
Package 1 Width	25.5 cm
Package 1 Length	42.0 cm
Package 1 Weight	3.5 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	42.2 cm
Package 2 Width	44.0 cm
Package 2 Length	52.8 cm
Package 2 Weight	13.308 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information