

Product data sheet

Characteristics

CLITPDL1C2B10

Downlight LED, 750lm, 3K/4K/6K Trim - 10 Pack



Main

Range	Clipsal
Product or component type	Downlight
Device application	Lighting
Market segment	Residential Small commercial

Complementary

Device mounting	Recessed ceiling
Shape	Round
Type of installation	Indoor
Rated power in W	9 W
Light source	LED
Total system power	240 V AC 50 Hz
Luminous flux	700 Lm 3000 K 4000 K 6000 K
Colour rendering index	R _a =80
Bulb lifespan	50000 h
Beam angle	90 °
Load type	Dimmable LED
Device composition	Round white plastic fixed integral dimming driver soft glow Flex plug
Quantity per set	10
Trim width	110 mm
Trim height	65.5 mm
Cut-out dimensions	90 mm
Mounting depth	62.5 mm
Net weight	0.25 kg

Environment

IP degree of protection	IP44
Insulation contact rating	IC-4
Unified glare rating	< 22
Ambient air temperature for operation	-10...25 °C
Relative humidity	non-condensing

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	20.5 cm
Package 1 Width	25.5 cm
Package 1 Length	42.0 cm
Package 1 Weight	3.5 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	42.2 cm
Package 2 Width	44.0 cm
Package 2 Length	52.8 cm
Package 2 Weight	13.308 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes