

Product data sheet

Characteristics

CLITPDL1C3

LED downlight, Clipsal - Lighting, 750lm, 3K/4K/6K, white



Main

Range	Clipsal
Product or component type	Downlight
Device application	Lighting
Market segment	Residential Commercial
Main colour tint	White
Colour tint	White

Complementary

Device mounting	Recessed ceiling
Shape	Round
Type of installation	Indoor/outdoor
Rated power in W	7 W
Light source	LED
Total system power	230 V AC 50 Hz
Luminous flux	750 Lm 3000 K warm white 750 Lm 4000 K cool white 750 Lm 6000 K day light
Colour rendering index	R _a =80
Bulb lifespan	50000 h
Beam angle	90 °
Load type	Dimmable LED
Quantity per set	1
Trim width	110 mm
Cut-out dimensions	90 mm
Mounting depth	55 mm
Net weight	0.2 kg

Environment

IP degree of protection	IP44
Insulation contact rating	IC-4
Unified glare rating	< 22
Ambient air temperature for operation	-10...25 °C
Relative humidity	10...95 % non-condensing

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9 cm
Package 1 Width	13 cm
Package 1 Length	13 cm
Package 1 Weight	264 g
Unit Type of Package 2	CAR
Number of Units in Package 2	24
Package 2 Height	30 cm
Package 2 Width	27.5 cm
Package 2 Length	54 cm
Package 2 Weight	6.972 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	3-Year
----------	--------