

## Product data sheet

### Characteristics

# CLITPDL2K4

Clipsal - LED downlight - 9W - 4000K - IP44 - white trim



### Main

Range	Clipsal
Product or component type	Downlight
Device application	Lighting
Market segment	Residential Small commercial

### Complementary

Device mounting	Recessed ceiling
Shape	Round
Type of installation	Indoor
Rated power in W	9 W
Light source	LED
Total system power	240 V AC 50 Hz
Luminous flux	950 lm 4000 K warm white
Colour rendering index	R <sub>a</sub> =80
Bulb lifespan	50000 h
Beam angle	90 °
Load type	Dimmable LED
Device composition	Plastic integral dimming driver Flex Plug Round white plastic fixed trim Light diffuser soft glow
Trim width	115 mm
Cut-out dimensions	90 mm
Mounting depth	61 mm

### Environment

IP degree of protection	IP44
Ambient air temperature for operation	-10...45 °C
Relative humidity	10...95 % non-condensing

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	275 g
Package 1 Height	70 mm
Package 1 width	125 mm
Package 1 Length	125 mm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>