

Product data sheet

Characteristics

CLITPDL2K4

Downlight LED, Clipsal - Lighting, 9W, 4000K, 950lm Trim



Main

Range	Clipsal
Product or component type	Downlight
Device application	Lighting
Market segment	Residential Small commercial

Complementary

Device mounting	Recessed ceiling
Shape	Round
Type of installation	Indoor
Rated power in W	9 W
Light source	LED
Total system power	240 V AC 50 Hz
Luminous flux	950 lm 4000 K warm white
Colour rendering index	R _a =80
Bulb lifespan	50000 h
Beam angle	90 °
Load type	Dimmable LED
Device composition	Plastic integral dimming driver Flex Plug Round white plastic fixed trim Light diffuser soft glow
Trim width	115 mm
Cut-out dimensions	90 mm
Mounting depth	61 mm

Environment

IP degree of protection	IP44
Ambient air temperature for operation	-10...45 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	12.5 cm
Package 1 Length	12.5 cm

Package 1 Weight	275.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	38.6 cm
Package 2 Width	27.0 cm
Package 2 Length	39.4 cm
Package 2 Weight	6.9 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information