


Product data sheet

Characteristics

CLITPFLH150LED

Floodlight LED, 150W, 6500K, 14,500lm, IP65



Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting

Complementary

Type of installation	Outdoor
Device mounting	Surface
Total system power	150 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	14500 lm
Colour rendering index	R _a =70
Bulb lifespan	30000 h
Colour temperature	6500 K
Beam angle	100 °
Electrical insulation class	Class I
Height	Body with trunion arm: 475 mm
Width	415 mm
Depth	102 mm
Net weight	7.0 kg

Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...45 °C
Relative humidity	10...95 % non-condensing

Contractual warranty

Warranty	3-Years
----------	---------