

Product data sheet

Characteristics

CLITPFLS10LED

Clipsal - Lighting, Floodlight LED, 10W, 4000K, 900lm



Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting

Complementary

Type of installation	Outdoor
Device mounting	Surface
Total system power	10 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	900 lm
Colour rendering index	R _a =70
Bulb lifespan	30000 h
Colour temperature	4000 K
Beam angle	100 °
Electrical insulation class	Class I
Height	Body with trunion arm: 86 mm
Width	116 mm
Depth	27 mm
Net weight	0.4 kg
Cable length	0.9 m

Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	2.6 cm
Package 1 Length	11.8 cm
Package 1 Weight	0.485 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	30

Package 2 Height	30.8 cm
Package 2 Width	34.6 cm
Package 2 Length	43.2 cm
Package 2 Weight	13.69 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	3-Years
----------	---------