

Product data sheet

Characteristics

CLITPFLS10LED

Floodlight LED, 10W, 4000K, 900lm, Black



Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting

Complementary

Type of installation	Outdoor
Device mounting	Surface
Total system power	10 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	900 lm
Colour rendering index	R _a =70
Bulb lifespan	30000 h
Colour temperature	4000 K
Beam angle	100 °
Electrical insulation class	Class I
Height	Body with trunion arm: 86 mm
Width	116 mm
Depth	27 mm
Product weight	0.4 kg
Cable length	0.9 m

Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.485 kg
Package 1 Height	82 mm
Package 1 width	26 mm
Package 1 Length	118 mm

Contractual warranty

Warranty

3-Years
