

## Product data sheet

### Characteristics

# CLITPFLS20LED

Floodlight LED, 20W, 4000K, 1800lm, Black



#### Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting

#### Complementary

Type of installation	Outdoor
Device mounting	Surface
Total system power	20 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	1800 lm
Colour rendering index	R <sub>a</sub> =70
Bulb lifespan	30000 h
Colour temperature	4000 K
Beam angle	100 °
Electrical insulation class	Class I
Height	Body with trunion arm: 122 mm
Width	166 mm
Depth	29 mm
Net weight	0.68 kg
Cable length	0.9 m

#### Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

#### Packing Units

Package 1 Weight	0.75 kg
------------------	---------

#### Contractual warranty

Warranty	3-Years
----------	---------