

Product data sheet

Characteristics

CLITPFLS50LED

Clipsal - Lighting, Floodlight LED, 50W, 4000K, 4500lm



Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting

Complementary

Type of installation	Outdoor
Device mounting	Surface
Total system power	50 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	4500 lm
Colour rendering index	R _a =70
Bulb lifespan	30000 h
Colour temperature	4000 K
Beam angle	100 °
Electrical insulation class	Class I
Height	Body with trunion arm: 155 mm
Width	210 mm
Depth	33 mm
Net weight	1.45 kg
Cable length	0.9 m

Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.0 cm
Package 1 Width	3.0 cm
Package 1 Length	21.0 cm
Package 1 Weight	1.7 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	8

Package 2 Height	23.6 cm
Package 2 Width	24.8 cm
Package 2 Length	52.0 cm
Package 2 Weight	11.6 kg

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	3-Years
----------	---------