

## Product data sheet

### Characteristics

# CLITPFLS50LED

Floodlight LED, 50W, 4000K, 4500lm, Black



### Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting

### Complementary

Type of installation	Outdoor
Device mounting	Surface
Total system power	50 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	4500 lm
Colour rendering index	R <sub>a</sub> =70
Bulb lifespan	30000 h
Colour temperature	4000 K
Beam angle	100 °
Electrical insulation class	Class I
Height	Body with trunion arm: 155 mm
Width	210 mm
Depth	33 mm
Net weight	1.45 kg
Cable length	0.9 m

### Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.7 kg
Package 1 Height	160 mm
Package 1 width	30 mm
Package 1 Length	210 mm

## Contractual warranty

---

Warranty

3-Years

---