

Product data sheet

Characteristics

CLITPHBM3

Clipsal - Lighting, Highbay LED, 150W, 5000K, 15,000lm, IP65



Main

Range	Clipsal
Product name	TPHB Series
Product or component type	High bay light
Device application	Lighting
Type of installation	Indoor/outdoor
Market segment	Industrial buildings Commercial

Complementary

Environmental characteristic	Harsh environment
Light source	LED 150 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =70
Luminous flux	15500 lm
Colour temperature	5000 K
Beam angle	110 °
Mounting mode	By hook
Provided equipment	Flex Plug
IP degree of protection	IP65
Electrical insulation class	Class I
Material	Die cast aluminium housing Acrylic lens
Width	404 mm
Diameter	220 mm
Net weight	5.2 kg

Environment

Total system power	160 W
Bulb lifespan	50000 h
Ambient air temperature for operation	-10...50 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	43 cm
Package 1 Length	46.7 cm
Package 1 Weight	5.26 kg