

Product data sheet

Characteristics

CLITPHBM3

Highbay LED, 150W, 5000K, 15,000lm, IP65



Main

Range	Clipsal
Product name	TPHB Series
Product or component type	High bay light
Device application	Lighting
Type of installation	Indoor/outdoor
Market segment	Industrial buildings Commercial

Complementary

Environmental characteristic	Harsh environment
Light source	LED 150 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =70
Luminous flux	15500 lm
Colour temperature	5000 K
Beam angle	110 °
Mounting mode	By hook
Provided equipment	Flex Plug
IP degree of protection	IP65
Electrical insulation class	Class I
Material	Die cast aluminium housing Acrylic lens
Width	404 mm
Diameter	220 mm
Product weight	5.2 kg

Environment

Total system power	160 W
Bulb lifespan	50000 h
Ambient air temperature for operation	-10...50 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	5.26 kg
Package 1 Height	155 mm
Package 1 width	430 mm
Package 1 Length	467 mm