

Product data sheet

Characteristics

CLITPLP3

LED Panel 36W, 4000K, 600 x 600mm



Main

Range	Clipsal
Product name	TPLP Series
Product or component type	Panel light
Device application	Lighting

Complementary

Type of installation	Indoor
Total system power	40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	3500 lm
Bulb lifespan	50000 h
Colour temperature	4000 K
Colour	White
Mounting mode	Ceiling
Light source	LED 36 W
Width	595 mm
Length	595 mm
Depth	11 mm
Net weight	3.2 kg

Environment

IP degree of protection	IP20
Relative humidity	10...95 % non-condensing
Ambient air temperature for operation	-10...50 °C
Targeted country	Australia New Zealand

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3200.0 g
Package 1 Height	7 cm
Package 1 Width	65 cm
Package 1 Length	65 cm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	3-Years
----------	---------