

## Product data sheet

### Characteristics

# CLITPLPDRV

## Driver for LED Panel, Clipsal - Lighting, Non Dimming

### Main

Range	Clipsal
Product name	TPLP Series
Product or component type	Panel light
Device application	Lighting

### Complementary

Type of installation	Indoor
Total system power	40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour	Black
Mounting mode	Ceiling
Light source	36 W



### Environment

IP degree of protection	IP20
Relative humidity	10...95 % non-condensing
Ambient air temperature for operation	-10...50 °C
Targeted country	Australia New Zealand

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	6 cm
Package 1 Length	16 cm
Package 1 Weight	220 g

### Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

### Contractual warranty

Warranty	3-Years
----------	---------