

Product data sheet

Characteristics

CLITPLPDRVDALI

Clipsal - Lighting, Driver for LED Panel DALI

Main

Range	Clipsal
Product name	TPLP Series
Product or component type	Panel light
Device application	Lighting

Complementary

Type of installation	Indoor
Total system power	40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour	Black
Mounting mode	Ceiling
Light source	36 W

Environment

IP degree of protection	IP20
Relative humidity	10...95 % non-condensing
Ambient air temperature for operation	-10...50 °C
Targeted country	Australia New Zealand

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	6 cm
Package 1 Length	16 cm
Package 1 Weight	220 g

Contractual warranty

Warranty	3-Years
----------	---------