

Product data sheet

Characteristics

CLITPTUFF1

Batten Toughend LED, Clipsal, 12W, 3000 K / 4000 K / 6500 K, IP54, 600mm



Main

Range	Clipsal
Product name	TPWP Series
Product or component type	Batten light
Device application	Lighting

Complementary

Type of installation	Outdoor
Total system power	12 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	1000 lm
Bulb lifespan	30000 h
Colour temperature	3000 K 4000 K 6500 K
Colour	Grey and white
Mounting mode	Ceiling
Electrical insulation class	Class II
Light source	LED
Shape	Rectangular
Height	115 mm
Width	96 mm
Length	675 mm
Product weight	1.6 kg

Environment

IP degree of protection	IP54
IK degree of protection	IK08
Relative humidity	10...95 %
Ambient air temperature for operation	-10...45 °C
Targeted country	Australia

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.