

## Product data sheet

### Characteristics

# CLITPTUFF1

Clipsal Lighting, Batten Tough LED, 600mm, IP54, CCT 3K/4K/6K



### Main

Range	Clipsal
Product name	TPWP Series
Product or component type	Batten light
Device application	Lighting

### Complementary

Type of installation	Outdoor
Total system power	12 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R <sub>a</sub> =80
Luminous flux	1000 lm
Bulb lifespan	30000 h
Colour temperature	3000 K 4000 K 6500 K
Colour	Grey and white
Mounting mode	Ceiling
Electrical insulation class	Class II
Light source	LED
Shape	Rectangular
Height	115 mm
Width	96 mm
Length	675 mm
Net weight	1.6 kg

### Environment

IP degree of protection	IP54
IK degree of protection	IK08
Relative humidity	10...95 %
Ambient air temperature for operation	-10...45 °C
Targeted country	Australia

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	9.4 cm
Package 1 Length	68.0 cm

Package 1 Weight	1.5 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	40.5 cm
Package 2 Width	21.5 cm
Package 2 Length	69.5 cm
Package 2 Weight	10.0 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>