

Product data sheet

Characteristics

CLITPWL1

6W LED Wall Light, 4000K, IP54, Single Silver Body



Main

Range	Clipsal
Product name	TPWL Series
Product or component type	Wall light
Device application	Lighting

Complementary

Type of installation	Outdoor
Total system power	6 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =70
Luminous flux	330 lm
Bulb lifespan	36000 h
Colour temperature	4000 K
Colour	Body: silver
Device mounting	Wall mounted
Mounting mode	Surface mounted
Electrical insulation class	Class I
Shape	Rectangular
Length	157 mm
Width	70 mm
Depth	108 mm
Net weight	0.6 kg
Targeted country	Australia New Zealand

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	649.75 g
Package 1 Height	165 mm
Package 1 width	85 mm
Package 1 Length	115 mm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration