

Product data sheet

Characteristics

CLITPWL2

Clipsal - Lighting, 12W LED Wall Light, 4000K, IP54, Twin, Silver Body



Main

| | |
|---------------------------|-------------|
| Range | Clipsal |
| Product name | TPWL Series |
| Product or component type | Wall light |
| Device application | Lighting |

Complementary

| | |
|--------------------------------|--------------------------|
| Type of installation | Outdoor |
| Total system power | 12 W |
| Light source | LED |
| [Ue] rated operational voltage | 240 V AC 50 Hz |
| Colour rendering index | R _a =70 |
| Luminous flux | 660 lm |
| Bulb lifespan | 36000 h |
| Colour temperature | 4000 K |
| Colour | Body: silver |
| Device mounting | Wall mounted |
| Mounting mode | Surface mounted |
| Electrical insulation class | Class I |
| Shape | Rectangular |
| Length | 239 mm |
| Width | 70 mm |
| Depth | 106 mm |
| Net weight | 1.0 kg |
| Targeted country | Australia New Zealand |




Environment

| | |
|---------------------------------------|--------------------------|
| IP degree of protection | IP54 |
| Ambient air temperature for operation | -10...40 °C |
| Relative humidity | 10...95 % non-condensing |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 26.1 cm |
| Package 1 Width | 8.1 cm |
| Package 1 Length | 11.2 cm |
| Package 1 Weight | 905.7 g |

Offer Sustainability

| | |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------|
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |