

Product data sheet

Characteristics

CLITPWP1

Clipsal Lighting, Batten Weatherproof LED, 600mm, IP65, CCT 3K/4K/6K, 20W



Main

Range	Clipsal
Product name	TPWP Series
Product or component type	Batten light
Device application	Lighting

Complementary

Type of installation	Outdoor
Total system power	20 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	2000 lm
Bulb lifespan	30000 h
Colour temperature	3000 K 4000 K 6500 K
Colour	Grey and white
Mounting mode	Ceiling
Electrical insulation class	Class I
Light source	LED
Shape	Rectangular
Height	68 mm
Width	105 mm
Length	650 mm
Net weight	1.0 kg

Environment

IP degree of protection	IP65
IK degree of protection	IK08
Relative humidity	10...95 %
Ambient air temperature for operation	-10...45 °C
Targeted country	Australia

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	10.8 cm
Package 1 Length	69.0 cm

Package 1 Weight	1.2 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	17.0 cm
Package 2 Width	34.5 cm
Package 2 Length	71.5 cm
Package 2 Weight	7.0 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes