

## Product data sheet

### Characteristics

# CLITPWP2EM

Batten Weatherproof LED, 1200mm, IP65,  
CCT 3K/4K/6K, P/Shift 40W/20W, Emergency



### Main

Range	Clipsal
Product name	TPWP Series
Product or component type	Batten light
Device application	Lighting
Battery type	LiFePO4

### Complementary

Type of installation	Outdoor
Total system power	44 W 22 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R <sub>a</sub> =80
Luminous flux	4000 Lm 2000 lm
Bulb lifespan	30000 h
Colour temperature	3000 K 4000 K 6500 K
Colour	Grey and white
Mounting mode	Ceiling
Electrical insulation class	Class I
Light source	LED
Autonomy	3 h
Charging time	16 h
Control type	Test button
Supply	Non-maintained
Shape	Rectangular
Height	68 mm
Width	105 mm
Length	1260 mm
Net weight	2.0 kg

### Environment

IP degree of protection	IP65
IK degree of protection	IK08
Relative humidity	10...95 %
Ambient air temperature for operation	-10...45 °C
Targeted country	Australia

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	10.8 cm
Package 1 Length	130.0 cm
Package 1 Weight	2.2 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	17.0 cm
Package 2 Width	23.0 cm
Package 2 Length	132.5 cm
Package 2 Weight	10.0 kg