

Product data sheet

Characteristics

CLITPWP2EM

Clipsal Lighting, Batten Weatherproof LED,
1200mm, IP65, CCT 3K/4K/6K, P/Shift
40W/20W, Emergency



Main

Range	Clipsal
Product name	TPWP Series
Product or component type	Batten light
Device application	Lighting
Battery type	LiFePO4

Complementary

Type of installation	Outdoor
Total system power	44 W 22 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	4000 Lm 2000 lm
Bulb lifespan	30000 h
Colour temperature	3000 K 4000 K 6500 K
Colour	Grey and white
Mounting mode	Ceiling
Electrical insulation class	Class I
Light source	LED
Autonomy	3 h
Charging time	16 h
Control type	Test button
Supply	Non-maintained
Shape	Rectangular
Height	68 mm
Width	105 mm
Length	1260 mm
Net weight	2.0 kg

Environment

IP degree of protection	IP65
IK degree of protection	IK08
Relative humidity	10...95 %
Ambient air temperature for operation	-10...45 °C
Targeted country	Australia

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	10.8 cm
Package 1 Length	130.0 cm
Package 1 Weight	2.2 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	17.0 cm
Package 2 Width	23.0 cm
Package 2 Length	132.5 cm
Package 2 Weight	10.0 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes