

Product data sheet

Characteristics

CLITPWPLED1

Weatherproof Batten LED, 20W, 5000K, IP65



Main

Range	Clipsal
Product name	TPWP Series
Product or component type	Batten light
Device application	Lighting
Battery type	LiFePO4

Complementary

Type of installation	Outdoor
Total system power	20 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	3800 lm
Bulb lifespan	50000 h
Colour temperature	5000 K
Mounting mode	Wall-mounted
Light source	LED 20 W
Autonomy	2 h
Charging time	16 h
Control type	Test button
Supply	Non-maintained
Focal length	900 mm
Height	90 mm
Width	140 mm
Length	1274 mm

Environment

IP degree of protection	IP65
IK degree of protection	IK08
Relative humidity	10...85 % non-condensing
Ambient air temperature for operation	-10...50 °C
Targeted country	Australia

Packing Units

Package 1 Weight	1531.600 g
Package 1 Height	96.000 mm
Package 1 width	143.000 mm
Package 1 Length	717.000 mm

