

## Product data sheet

### Characteristics

# CLITPWPLED2EM

Clipsal Actassi, Weatherproof Batten LED,  
40W, 5000K, IP65 - Emergency



### Main

Range	Actassi
Product or component type	Batten light
Device application	Residential Commercial
Battery type	LiFePO4

### Complementary

Operational power in W	45 W
Light source	LED 40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	3800 lm
Bulb lifespan	50000 h
Colour temperature	5000 K
Autonomy	2 h
Charging time	16 h
Control type	Test button
Supply	Non-maintained
Device mounting	Surface
Mounting mode	By screws
IP degree of protection	IP65
Length	1274 mm
Width	140 mm
Height	90 mm
Distance between centers	900 mm
Net weight	2.65 kg

### Environment

Colour rendering index	R <sub>a</sub> =80
Ambient air temperature for operation	-10...50 °C
Relative humidity	10...85 %

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	14.3 cm
Package 1 Length	133.3 cm
Package 1 Weight	2949 g

