

## Product data sheet

### Characteristics

# CLITPWPLED2EM

Clipsal - LED weatherproof batten, 40W, 3800 lm, 5000K, IP65, 1200mm, Emergency



### Main

Range	Actassi
Product or component type	Batten light
Device application	Residential Commercial
Battery type	LiFePO4

### Complementary

Operational power in W	45 W
Light source	LED 40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	3800 lm
Bulb lifespan	50000 h
Colour temperature	5000 K
Autonomy	2 h
Charging time	16 h
Control type	Test button
Supply	Non-maintained
Device mounting	Surface
Mounting mode	By screws
IP degree of protection	IP65
Length	1274 mm
Width	140 mm
Height	90 mm
Distance between centers	900 mm
Net weight	2.65 kg

### Environment

Colour rendering index	R <sub>a</sub> =80
Ambient air temperature for operation	-10...50 °C
Relative humidity	10...85 %

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.