

Product data sheet

Characteristics

CLITUFF112LED

Clipsal - LED weatherproof Batten, 12W, 4000K, IP54, Grey base with Opal Diffuser



Main

Range	Clipsal
Product name	TUFF Series
Product or component type	Batten light
Device application	Secure lighting

Complementary

Type of installation	Outdoor
Total system power	12 W
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =80
Luminous flux	900 lm
Bulb lifespan	50000 h
Colour temperature	4000 K
Mounting mode	Wall-mounted
Light source	LED
Height	116 mm
Width	96 mm
Length	675 mm
Net weight	1.6 kg

Environment

IP degree of protection	IP54
Relative humidity	10...95 % non-condensing
Ambient air temperature for operation	0...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	10.0 cm
Package 1 Length	67.5 cm
Package 1 Weight	1.8 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration