

Product data sheet

Characteristics

CLP5010WDZ

Clipsal Wiser, Micro Module Smart Dimmer 200 W Max, 240 V, Grey



Main

Product brand	Clipsal
Range	Iconic
Product or component type	Connected dimmer

Complementary

Concentrator compatibility	Wiser hub generation 1
Mobile App name	Wiser by SE
Device presentation	Module
Device application	Light control
Dimmer type	Universal
Load type	Dimmable LED: 0...150 W Compact fluorescent lamp: 0...200 W Incandescent lamp: 0...200 W at 240 V Halogen lamp: 0...200 W at 240 V LV halogen lamps: 0...200 W (electronic transformer)
[Ue] rated operational voltage	220...240 V AC 50 Hz
Protection type	Overheating protection Short-circuit protection Overcurrent protection
Colour tint	Grey
Surface finish	Matt
Control type	Push-button By mobile application
Number of ways	5 ways
Software name	Wiser by SE App
Technology type	Zigbee
Communication network type	Wireless Zigbee (2.4 GHz), 2.5 mW at < 50 m
Wiring configuration	2-wire
Material	Plastic
Mounting support	Wall Installation box
Type of installation	Indoor installation
Embedding depth	40 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP20
Relative humidity	5...90 % non-condensing
Standards	AS/NZS 60669.2.1 safety AS/NZS 60669.2.1 EMC AS/NZS 4268 radio

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	80.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.68 kg
Unit Type of Package 3	P06
Number of Units in Package 3	640
Package 3 Height	75.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	73.88 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information