

## Product data sheet

### Characteristics

# DCBM2-1608

Clipsal C-Bus, BM-DALI 2 Line Controller, 16 Input, 8 Output



### Main

Range	DALI Control
Product or component type	Line control device
Device application	Control

### Complementary

Device composition	RJ45 connector - to supply the gateway via Ethernet CAT5 cable Serial cable Real time clock
Function available	Auto daylight savings adjustment Scheduling Monitor occupancy status Daylight harvesting Computer control Sunrise/Sunset in schedules Holiday schedules (20) Scene control (32) Ballast control (128) Group control (128)
Number of inputs	16
Control type	Touch screen Push-button Switch
Transmission support medium	Radio frequency
Suitable for sensor type	Occupancy sensor Light level sensor
Number of outputs	8 digital
Number of lines controlled	2
Data recording	32 sequence of event recording
Height	92 mm
Depth	63 mm
Width	216 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.6 cm
Package 1 Width	10.6 cm
Package 1 Length	22.3 cm
Package 1 Weight	540.0 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>