

Product data sheet

Characteristics

DI-SI20

2.0 METRE INTER CONNECT LEAD WITH DALI INFINITY FEMALE AND MALE CONNECTOR



Main

Product brand	Clipsal
Range of product	DALI Infinity
Colour	Contact: pastel blue Housing: black
Device application	Interlocking

Complementary

[Ue] rated operational voltage	250 V
[In] rated current	20 A
Number of poles	5
Cable stiffness	Stranded
Connector type	1 - 2 ways socket - 2 ways plug-in
Length	2000 mm
Interlocking type	Mechanical
Type of cable	H05VV-F
Cable outer diameter	12.3 mm
Poles description	P + E + N
Connections - terminals	Cable 3, cable cross section: 2.5 mm ² Cable 2, cable cross section: 1.5 mm ²
Contacts material	Silver plated contacts

Environment

IP degree of protection	IP40
Temperature resistance	100 °C
Environmental characteristic	Halogen free
Pollution degree	2

Packing Units

Package 1 Weight	0.500 kg
Package 1 Height	10.000 mm
Package 1 width	40.000 mm
Package 1 Length	2000.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration