

Product data sheet

Characteristics

DI-SI40

4.0 METRE INTER CONNECT LEAD WITH DALI INFINITY FEMALE AND MALE CONNECTOR



Main

Product brand	Clipsal
Range of product	DALI Infinity
Colour	Contact: pastel blue Housing: black
Device application	Interlocking

Complementary

[Ue] rated operational voltage	250 V
[In] rated current	20 A
Number of poles	5
Cable stiffness	Stranded
Connector type	1 - 2 ways socket - 2 ways plug-in
Length	4000 mm
Interlocking type	Mechanical
Type of cable	H05VV-F
Cable outer diameter	12.3 mm
Poles description	P + E + N
Connections - terminals	Cable 3, cable cross section: 2.5 mm ² Cable 2, cable cross section: 1.5 mm ²
Contacts material	Silver plated contacts

Environment

IP degree of protection	IP40
Temperature resistance	100 °C
Pollution degree	2

Packing Units

Package 1 Weight	1.000 kg
Package 1 Height	10.000 mm
Package 1 width	40.000 mm
Package 1 Length	4000.000 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration