

## Product data sheet

### Characteristics

# DI-SI70

## 7.0 METRE INTER CONNECT LEAD WITH DALI INFINITY FEMALE AND MALE CONNECTOR



### Main

Product brand	Clipsal
Range of product	DALI Infinity
Colour	Contact: pastel blue Housing: black
Device application	Interlocking

### Complementary

[Ue] rated operational voltage	250 V
[In] rated current	20 A
Number of poles	5
Cable stiffness	Stranded
Connector type	1 - 2 ways socket - 2 ways plug-in
Length	7000 mm
Interlocking type	Mechanical
Type of cable	H05VV-F
Cable outer diameter	12.3 mm
Poles description	P + E + N
Connections - terminals	Cable 3, cable cross section: 2.5 mm <sup>2</sup> Cable 2, cable cross section: 1.5 mm <sup>2</sup>
Contacts material	Silver plated contacts

### Environment

IP degree of protection	IP40
Temperature resistance	100 °C
Pollution degree	2

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	4 cm
Package 1 Length	700 cm
Package 1 Weight	1.75 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>