

Product data sheet

Characteristics

DL1BLE

Harmony XVD, Lamp, BA15D, 48V, 10W



Main

| | |
|---------------------------------------|---------------------------|
| Range compatibility | Harmony XVD |
| Accessory / separate part designation | Incandescent bulb |
| Accessory / separate part type | Incandescent bulb |
| Accessory / separate part category | Lighting accessories |
| Accessory / separate part destination | Beacon and indicator bank |
| [Us] rated supply voltage | 48 V |
| Signalling type | Steady |
| Power dissipation in W | 10 W |
| Sale per indivisible quantity | 10 |

Complementary

| | |
|------------|---------|
| Bulb base | BA 15d |
| Net weight | 0.09 kg |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4.8 cm |
| Package 1 Width | 6.4 cm |
| Package 1 Length | 13.0 cm |
| Package 1 Weight | 9.0 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 4.8 cm |
| Package 2 Width | 6.4 cm |
| Package 2 Length | 13.0 cm |
| Package 2 Weight | 90.0 g |
| Unit Type of Package 3 | S02 |
| Number of Units in Package 3 | 120 |
| Package 3 Height | 15.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 1.456 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|