

## Product data sheet

### Characteristics

# E02/20/2

## CLIPSAL RCD/MCB AND audible Alarm - flush mount - 2P -20A - 10mA



### Main

Range	Medilec Clipsal - Series E02
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
[In] rated current	20 A
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Class AC

### Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	240 V AC
Protection type	Short time short-circuit protection
Mounting mode	Flush mounting
Size	220 x 175 x 70 mm conforming to DIN 43880




### Environment

Standards	AS/NZS 3190
Ambient air temperature for operation	-10...55 °C

### Packing Units

Package 1 Weight	1.440 kg
------------------	----------

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.