

Product data sheet

Characteristics

E14/36/2

Medilec, Isolation Transformers, 240V, 3.6kVA, Encapsulated

Main

Product brand	Clipsal
---------------	---------

Complementary

Primary voltage	240 V AC
Secondary voltage	240 V AC
Rated power in VA	3600 VA
[In] rated current	15 A

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26.5 cm
Package 1 Width	30.0 cm
Package 1 Length	28.5 cm
Package 1 Weight	40.0 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.