

Product data sheet

Characteristics

E14/36/3

TRANS E14 3.6KVA (NON EPOXY)



Main

Product brand	Clipsal
---------------	---------

Complementary

Primary voltage	240 V AC
Secondary voltage	240 V AC
Rated power in VA	3600 VA
[In] rated current	15 A

Packing Units

Package 1 Weight	35.000 kg
------------------	-----------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.