

# Product data sheet

## Characteristics

# E14/48/3

## TRANS E14 4.8KVA (NON EPOXY)



### Main

Product brand	Clipsal
---------------	---------



### Complementary

Primary voltage	240 V AC
Secondary voltage	240 V AC
Rated power in VA	4800 VA
[In] rated current	20 A

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	41.16 kg
Package 1 Height	30.2 cm
Package 1 width	27.2 cm
Package 1 Length	31.2 cm

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.