

Product data sheet

Characteristics

E2215FBP

Switchboard metal back plate, MAX9, type 2, 2 row



Main

Range	MAX9
Product or component type	Back plate

Complementary

Number of horizontal rows	2
Height	371 mm
Width	280 mm
Enclosure material	Galvanized steel
Depth	1.6 mm
Provided equipment	(1) plate (4) screws Earthing wire




Environment

Standards	AS/NZS 3000
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.453 kg
Package 1 Height	2.3 cm
Package 1 width	28 cm
Package 1 Length	37.1 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
