

## Product data sheet

### Characteristics

# E2315FBP

## Switchboard Metal Back Plate, MAX9, Type 2, 3 Row



### Main

Range	MAX9
Product or component type	Back plate

### Complementary

Height	600 mm
Number of horizontal rows	3
Width	252 mm
Enclosure material	Galvanized steel
Depth	1.6 mm
Provided equipment	(1) plate (4) screws Earthing wire

### Environment



Standards	AS/NZS 3000
-----------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	25.25 cm
Package 1 Length	60.0 cm
Package 1 Weight	2.076 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	7-year
----------	--------