

Product data sheet

Characteristics

E2415FBP

Clipsal MAX9, Switchboard Metal Back Plate, Type 2, 4 Row



Main

Range	MAX9
Product or component type	Back plate

Complementary

Number of horizontal rows	4
Height	740 mm
Width	284 mm
Enclosure material	Galvanized steel
Depth	1.6 mm
Provided equipment	(1) plate (4) screws Earthing wire

Environment



Standards	AS/NZS 3000
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	28.4 cm
Package 1 Length	74.0 cm
Package 1 Weight	2.845 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	7-year
----------	--------
