

## Product data sheet

### Characteristics

# E2415FBP

Switchboard metal back plate, MAX9, type 2, 4 row



### Main

Range	MAX9
Product or component type	Back plate

### Complementary

Number of horizontal rows	4
Height	740 mm
Width	284 mm
Enclosure material	Galvanized steel
Depth	1.6 mm
Provided equipment	(1) plate (4) screws Earthing wire




### Environment

Standards	AS/NZS 3000
-----------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.845 kg
Package 1 Height	2.3 cm
Package 1 width	28.4 cm
Package 1 Length	74 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>

---

China RoHS Regulation

 [China RoHS Declaration](#)

---

Environmental Disclosure

 [Product Environmental Profile](#)

---