

Product data sheet

Characteristics

E3015/4C-AW

Clipsal Iconic, cover frame, 4 switches & 4 sockets, 10 A, hori, arctic white



Main

Range	Clipsal Iconic
Aesthetic name	Iconic Essence
Product or component type	Cover frame
Colour tint	Cover frame: arctic white (AW) Edge: birch
Type of packing	Polybag
Quantity per set	Set of 5

Complementary

Range compatibility	Switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	4
Number of power socket outlets	4
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Matt
Material	Birch timber: cover frame
Height	86.0 mm
Width	227.0 mm
Depth	9.0 mm
Net weight	0.06 kg

Environment

Ambient air temperature for storage	0...45 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	62.0 g
Package 1 Height	1 cm
Package 1 width	8.2 cm
Package 1 Length	22.2 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile