

Product data sheet

Characteristics

E3025C-AG

Clipsal Iconic, cover frame, 2 switches & 2 sockets, 10 A, hori, ash grey



Main

Range	Clipsal Iconic
Aesthetic name	Iconic Essence
Product or component type	Cover frame
Colour tint	Cover frame: ash grey (AG) Edge: dark stained
Type of packing	Polybag
Quantity per set	Set of 10




Complementary

Range compatibility	Switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	2
Number of power socket outlets	2
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Matt
Material	Birch timber: cover frame
Height	85.0 mm
Width	131.0 mm
Depth	9.0 mm
Net weight	0.03 kg

Environment

Ambient air temperature for storage	0...45 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
