

Product data sheet

Characteristics

E3046C-AG

Clipsal Iconic, Essence Switch Plate Skin, 6 Gang, Vertical/Horizontal, Clip-On



Main

Range	Clipsal Iconic
Aesthetic name	Iconic Essence
Product or component type	Cover frame
Colour tint	Cover frame: ash grey (AG) Edge: dark stained
Type of packing	Polybag
Quantity per set	Set of 10

Complementary

Range compatibility	Clipsal Iconic switch
Product destination	Switch
Device mounting	Flush
Number of rocker	6
Installation direction	Vertical
Fixing mode	Clip-on
Surface finish	Matt
Material	Birch timber: cover frame
Height	131.0 mm
Width	85.0 mm
Depth	8.5 mm
Net weight	0.03 kg

Environment

Ambient air temperature for storage	0...45 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	8.5 cm
Package 1 Length	13.0 cm
Package 1 Weight	44.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations