

Product data sheet

Characteristics

E3046C-AW

Skin Switch Iconic Essence - 6-gang - Arctic White



Main

Range	Clipsal Iconic
Aesthetic name	Iconic Essence
Product or component type	Cover frame
Colour tint	Cover frame: arctic white (AW) Edge: birch
Type of packing	Polybag
Quantity per set	Set of 10

Complementary

Range compatibility	switch
Product destination	Switch
Device mounting	Flush
Number of rocker	6
Installation direction	Vertical
Fixing mode	Clip-on
Surface finish	Matt
Material	Birch timber: cover frame
Height	131.0 mm
Width	85.0 mm
Depth	8.5 mm
Net weight	0.03 kg

Environment

Ambient air temperature for storage	0...45 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	44.0 g
Package 1 Height	1 cm
Package 1 width	8.5 cm
Package 1 Length	13 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile