

## Product data sheet

### Characteristics

# E31/2SA-WE

## Standard Series, Switch Flush 1 Gang 2 Way 10Ax



### Main

Range of product	Standard Series
Product brand	Clipsal
Device presentation	Basic element with full cover plate

### Complementary

Switch function	2-way
Number of rocker	1
Device mounting	Flush
Local signalling	without
Rated current	10 AX, fluorescent lamp
Actuator	Rocker

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	8.4 cm
Package 1 Length	8.4 cm
Package 1 Weight	12 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	8.5 cm
Package 2 Width	14.4 cm
Package 2 Length	17.9 cm
Package 2 Weight	0.12 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	18.2 cm
Package 3 Width	30.8 cm
Package 3 Length	45.3 cm
Package 3 Weight	1200 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>