

Product data sheet

Characteristics

E319-WE

Standard Series, Switch Time Delay



Main

Colour	White electric
Product brand	Clipsal
Range of product	Series 319
Device presentation	Basic element with full cover plate

Complementary

Colour code	WE
Device mounting	Flush
Material	Plastic
Surface finish	Glossy
Autonomy	0.0083...0.33 h
[Ue] rated operational voltage	250 V
Network frequency	50/60 Hz
Rated current	10 A

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	8.4 cm
Package 1 Length	8.4 cm
Package 1 Weight	0.106 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	14 cm
Package 2 Width	16.1 cm
Package 2 Length	28 cm
Package 2 Weight	1.34 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	30.5 cm
Package 3 Width	29.6 cm
Package 3 Length	43.6 cm
Package 3 Weight	6550 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes