

## Product data sheet

### Characteristics

# E40BD3R-AW

## Clipsal Iconic Essence Rocker BED3



### Main

Range of product	Clipsal Iconic
Aesthetic name	Iconic Essence
Product or component type	Rocker
Colour	Arctic white (AW)
Type of packing	Polybag
Quantity per set	Set of 1
Sale per indivisible quantity	1.0

### Complementary

Product destination	Switch
Fixing mode	Clip-in
Marking	BED3
Surface finish	Matt
Height	23.0 mm
Width	23.0 mm
Depth	2.0 mm
Net weight	0.01 kg

### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	1.8 cm
Package 1 Length	2.3 cm
Package 1 Weight	1.88 g
Unit Type of Package 2	BAG
Number of Units in Package 2	5
Package 2 Height	1 cm
Package 2 Width	9.8 cm
Package 2 Length	19 cm
Package 2 Weight	11.9 g
Unit Type of Package 3	Gyári csomagolás
Number of Units in Package 3	50
Package 3 Height	16.7 cm
Package 3 Width	10.5 cm
Package 3 Length	13 cm
Package 3 Weight	173 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>