

Product data sheet

Characteristics

EY56C315

Easy56, Switched Socket, 3 Pin, 15A, 250V



Main

Product name	Easy56
Product or component type	Switch and socket-outlet
Device short name	EY56C315
Plug, socket category	Low voltage
Poles description	1P + N + E
Control type	Rotary knob
Rotary handle padlocking	2 padlocks 8 mm
Network type	AC
Outlet standard	Australian/New Zealand

Complementary

Mounting mode	Surface mounted
Plug, socket, control station shape	Straight
[In] rated current	15 A
Pin number	3 pins
Shape of pin	Flat
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Protection type	Without protection
Material	Polycarbonate
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals
Cable cross section	1.5...6 mm ²
Cable entry number	2 x M25 1 x M32
Net weight	0.82 kg
Height	203 mm
Width	101 mm
Depth	101 mm
Colour	Body: grey (RAL 7035) Rotary handle: dark grey

Environment

Standards	AS/NZS 3112 AS/NZS 3133
Quality labels	RCM
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.4 cm
Package 1 Width	10.4 cm
Package 1 Length	20.7 cm
Package 1 Weight	861 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.8 cm
Package 2 Width	35.3 cm
Package 2 Length	45 cm
Package 2 Weight	10532 g
Unit Type of Package 3	PAL
Number of Units in Package 3	240
Package 3 Height	100 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	224640 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes