

Product data sheet

Characteristics

EY56C420

Easy56 Switched Socket - 4 Pin - 20A - 500V



Main

Product name	Easy56
Product or component type	Switch and socket-outlet
Device short name	EY56C420
Plug, socket category	Low voltage
Poles description	3P + E
Control type	Rotary knob
Rotary handle padlocking	2 padlocks 8 mm
Network type	AC
Outlet standard	Australian/New Zealand

Complementary

Mounting mode	Surface mounted
Plug, socket, control station shape	Straight
[In] rated current	20 A
Pin number	4 pins
Shape of pin	Tubular
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Protection type	Without protection
Material	Polycarbonate
Contacts material	Pins: brass
Connections - terminals	Screw terminals
Cable cross section	1...16 mm ²
Cable entry number	2 x M25 1 x M32
Product weight	0.82 kg
Height	203 mm
Width	101 mm
Depth	101 mm
Colour	Body: grey (RAL 7035) Rotary handle: dark grey

Environment

Standards	AS/NZS 3133 AS/NZS 3123
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

Packing Units

Package 1 Weight	944.000 g
Package 1 Height	114.000 mm
Package 1 width	105.000 mm
Package 1 Length	208.000 mm

